

## Livello laterale

F.lli Giacomello punta a presentare sul mercato prodotti in grado di monitorare e visualizzare il passaggio dei fluidi nel modo più preciso e affidabile possibile. Il livello laterale RL/L-P-RL/LF è l'esempio perfetto. Si contraddistingue per la sua praticità e per la sua sicurezza. Le dimensioni ridotte permettono all'utilizzatore di posizionarlo nei punti più difficili. Come il Rapid Level Laterale, anche questo livello va inserito direttamente nel punto che si desidera controllare. I contatti sono N.A. o N.CH. in assenza di liquido (la reversibilità si ottiene ruotando il livello di 180°) oppure a richiesta in scambio. La composizione in PVDF permette al livello di resistere a liquidi aggressivi come acido solforico, acido nitrico, acido cloridrico, benzine, propano, tutti i tipi di alcool, purché privi di particelle ferrose, in quanto il magnete è in prossimità del liquido. La saldatura effettuata a ultrasuoni sia sul galleggiante sia sul corpo livello con relativa basetta porta contatti garantisce una perfetta tenuta dei vari componenti.



## Side level switch

*The purpose of F.lli Giacomello is to present on the market products capable of monitoring and displaying the passage of fluids in the most precise and reliable way possible. The RL/L-P-RL/LF side level switch is the perfect example. It stands out for its practicality and safety. The small size allows the user to position it in the most difficult points. Like the Lateral Rapid Level, this level switch must also be inserted directly in the point you want to check.*

*The contacts are N.A. or N.CH. in the absence of liquid - reversibility is obtained by rotating the level by 180° - or on request in exchange. The PVDF composition allows the level to resist aggressive liquids such as sulfuric acid, nitric acid, hydrochloric acid, gasoline, propane, all types of alcohol, as long as they are free of ferrous particles, as the magnet is close to the liquid. The ultrasonic welding carried out both on the float and on the level body with its contact holder base guarantees a perfect seal of the various components.*